

S-MicroW L Ultra Freeze

S-MicroW L Ultra Freeze is a data logger for ultra low temperatures from -80°C to 140°C (calibration from -40°C to 140°C) with 20, 100 mm or on demand length external probe (probes cannot be switched) on a 5 mm base (base height is not counted for probe length), managed with Windows software and USB interface (DiskInterface HS, Multibay). **Battery is user replaceable** and the data logger is **provided with an Accredia (NIST equivalent) traceable certificate** on 6 points.

The data logger looks like the S-MicroW L standard but it includes a calibration from -40°C. With calibration from -40°C it can be used also at -80°C with an accuracy within $\pm 0,5$ °C within range -80 °C ÷ -40 °C. If -80°C is requested to be on the certificate, an extra calibration point for very low temperatures must be purchased. It is particularly indicated for monitoring and **validation of ultra freezers**.

The other versions of the data logger are:

- S-MicroW L: with rigid probe of different lengths
- S-MicroW L Flexible: with flexible cable probe and rigid probe at the end
- S-MicroW L Bendable: with semi-rigi metal bendable probe and rigid probe at the end

For each version it is available the XL model too, S-MicroW XL Ultra Freeze, which has same diameter but is higher because it hosts a bigger battery for a longer life time.

There are also other models of high temperature data loggers, for pressure and humidity too.

Note: if used below -30°C, battery life will be highly reduced. Mission max duration at -80°C: 12 hours. Using the logger for long periods below -40°C will constantly reduce mission max duration. For longer missions purchase the -80°C special battery for S-MicroW L Ultra Freeze. With -80°C special battery mission max duration at -80°C with the special battery: 2 months. Using the logger for long periods below -40°C will constantly reduce mission max duration. Max temperature of use of the -80°C battery is 80°C: REMOVE IT AND USE STANDARD BATTERY TO USE THE LOGGER IN AUTOCLVE OR ABOVE 80°C.

Main features

- With different lengths rigid probe for penetration
- Completely food grade and waterproof
- **All software calculate lethality value (F0, PU, A0 ecc.)**
- Low battery consumption for an extended battery life
- User replaceable battery (**software shows battery status**)
- Very easy to deploy in any type of package
- Accredia (NIST equivalent) traceable calibration certificate included **from -40°C**
- Available **extended calibration from -80°C** (order extra calibration points; in case of wide calibration range the accuracy might be worse)

Plus

- Extremely high accuracy and precision: with an accuracy of $\pm 0,1$ °C these devices can be employed in any application involving pharmaceuticals, validation, laboratory and medical field
- High accuracy even outside the calibration range
- Save money on calibration costs with calibration from -40°C included
- High accuracy even from -80°C
- Fast response time thanks to the 3 mm diameter probe



Applications



Validation



Sterilisation



Pharmaceutical



Healthcare



Medical



Laboratories



Food & Beverages



Pasteurisation

- Printed reports compliant with health regulations and ISO (data are not editable in the software)

The system

The system is made up by:

- S-MicroW L temperature data logger
- DiskInterface HS or Universal Multibay
- SPD software or TS Manager software (compatible with the FDA 21 CFR Part 11 regulation)

Accessories

- SPD
- TS Manager
- Tecno Calib
- DiskInterface HS
- Universal multibay
- Locking bolt
- Fastening system
- Teflon protective tube
- S-MicroW L battery kit
- S-MicroW L Ultra Freeze -80°C battery kit

Technical specifications

| | |
|---|---|
| Dimensions | 39 h X 20 Ø (mm) |
| Probe dimensions | Probe base dimensions 5 h X 14 Ø (mm) - Probe 20/100 l X 3 Ø (mm) - - Probe l on demand X 3 Ø (mm) (l on demand: min. 10 mm / max. 175 mm. For longer probes ask for quotation) |
| Weight | 50 gr |
| Materials | Stainless steel AISI316L, PEEK |
| Temperature range | -80 °C ÷ +140 °C |
| Standard calibration points (temperature) | -40/-20/0/25/50/75/100/125/140°C |
| Extra calibration points (temperature) | Within the range -80 °C ÷ +140 °C |
| Temperature resolution | 0,01 °C |
| Temperature accuracy | ± 0,1 °C (within the calibration range) |
| Memory (n. of acquisitions) | 20.224 |
| Acquisition step | From 1 every second up, with 1 second steps |
| Protection degree | IP68 |
| Battery life | +10.000.000 acquisitions at 1 second step continuously (calculated time @25°C. Battery life may be shorter if used in low temperatures) |
| Software&Mobile App | SPD, TS Manager |
| Accessories | DiskInterface HS, Multibay universale |



Tecnosoft srl
Via Galvani, 4, 20068, Peschiera Borromeo (MI), Italy
T: (+39) 02 2692 2888 - F: (+39) 02 2692 2875
email: info@tecnosoft.eu - web: www.tecnosoft.eu
UNI EN ISO 9001:2008 Certiquality/IQNet N. 17733

